

Cascade CM300xi with MHU301

300 mm Fully-automated Probe System with Contact Intelligence™ Technology

High-Temperature Stability (HTS) probe card holder (option)*

- Ensures EMI-shielded and light-tight environment for the probe card for higher measurement accuracy
- Rigid and thermally optimized design, for reliable small pad probing
- Easy change-over to analytical measurement set-up with TopHat™

Material Handling Unit (MHU301)

- For fast handling of 200/300 mm wafers
- Integrated pre-aligner for flat/notch detection
- Barcode/2D Matrix code/OCR wafer code recognition from both sides (option)
- Quick Access Port option for higher throughput and additional wafer storage
- Smallest footprint to save precious lab space
- Available for CM300 at left or right side

SEMI-compliant load port

- For enhanced capacity of up to 25 wafers for extended autonomous operation
- For FOUP and FOSB 300 mm wafer cassettes
- Open cassette adapter for use of standard 200 mm wafer cassettes (option)
- AutoInventory and cassette hot-swap capability for high-priority wafer test processing

For maximum productivity




Dual-prober configuration with MHU300

- Two independent prober systems share a single handling unit, enabling greater test cell efficiency and minimizing footprint

*Contact Intelligence technology enables unattended test over multiple temperatures:

- VueTrack™ closed-loop positioning capability minimizes the need of manual re-adjustment when probing small pads across multiple temperatures.
- Velox probe station software provides a single command interface for automated temperature transitions continuously managing the separation between probes and pad during temperature ramp.
- Velox probe station software provide the ability to optimize the soak time after a temperature transition or when stepping across the wafer based on the temperature variance.
- Realign option is much faster due to the fast focus scan, which minimizes the thermally-induced drift during off-axis alignment of prober and pads.
- High-Temperature Stability (HTS) microscope bridge enables automated test over multiple temperatures.
- HTS platen provides stability over a wide thermal probing range.
- HTS probe card holder ensures EMI-shielded and light-tight environment, achieving accurate and reliable small-pad probing (option).
- As an additional option, the Contact Intelligence DC Motorized Positioner Package includes VueTrack Pro, motorized positioners with friction-less EMI shielding and HTS probe arms, enabling unattended testing on small pads across multiple temperatures. This is an ideal option for customers working with high-mix/low-volume device layouts requiring flexible positioner-based setups.



Full-featured prober system

- Full EMI-shielding for highly-accurate low-leakage and low-noise measurement results
- Minimizes settling times for efficient measurements, without compromising accuracy over full thermal range
- Automated Thermal Management (ATM™) sets equipment parameter relative to chuck temperature
- Automated re-alignment capability compensates thermal drift of wafers and probes after every temperature change. Reliable and repeatable contacts over a wide thermal range on small pads down to 30 μm and microbumps
- High-Temperature Stability microscope bridge enabling automated testing over temperature*

Velox™ probe station control software

- Operate machine in a semi-automatic engineering mode
- Free die-to-die navigation on wafer and testing
- Integrated wafer handling, alignment, temperature control, z-profiling and stepping capabilities
- Automated wafer alignment, and auto XYZ and theta correction for sub-micron stepping

VeloxPro™ test automation software

- Easy-to-use SEMI E95 compliant user interface
- Efficient communication with test executive software

Rollout stage with quick access to auxiliary sites

- Full wafer access via locking roll-out stage
- Two patented auxiliary chucks for high calibration accuracy for RF/mmW measurements
- Three sites for advanced cleaning procedures and contact verification

3D Manual Controls

- Virtual Platen Lift and XY knobs at front for intuitive, and precise movement of chuck in X, Y, and Z-direction
- Platen Lift enables extremely rapid and intuitive way in performing many alignment tasks, like setting up the contact height

Built-in vibration-isolation system

- Eliminates vibration from external sources, such as acoustic and architectural, enabling reliable small pad probing
- Enhances system stability and reduces damage to pads, wafers and probe tips
- Easy access from front- and back-side for fast configuration and service

The image shown and features listed above are based on the fully-shielded version of CM300xi (CM300xi-F) with additional options. FormFactor also offers CM300xi-S (shielded system) and CM300-O (open system). For more details, please refer to CM300xi Data Sheet.

Probing over wide thermal range

- Thermal range -60°C to 300°C for characterization and modeling
- High-Temperature Stability platen, shielding solution and ultra-flat wafer chucks ensure stable and repeatable measurements*

©Copyright 2020, FormFactor, Inc. All rights reserved. FormFactor and the FormFactor logo are trademarks of FormFactor, Inc. All other trademarks are the property of their respective owners. All information is subject to change without notice.